

Project Name

Location

Prepared By



## NUVO 60-7748

TERRACE 1 LIGHT WALL SCONCE

### Notes

[www] 07-05-2023 01:10:03

### General

Status	Active
Collection	Terrace
Finish	Matte Black
Style	Contemporary
Number of Lamps	1
Height (in.)	24.00
Width (in.)	4.50
Extension (in.)	5.63
Indoor or Outdoor Fixture	Indoor

### Specifications

Base	Medium
Bulb Type	Incandescent
Max Wattage	60W
Bulb Included	No
Glass Description	Crackle
Weight (lb.)	3.30
Up/Down Installation	Up or Down
Fixture Shape	Linear
Fixture Type	Wall Sconce
Fixture Material	Steel

### Dimensions

Back Plate or Canopy Width (in.)	4.50
Back Plate or Canopy Height (in.)	4.50
Top to Outlet	11.75

### Compliance

Safety Listing	cULus - Listed
Location Rating	Damp
Energy Star	No
DLC Approved	No
California Prop 65	Lead

### Additional Information

Warranty	1 Year Limited - Fixtures
----------	---------------------------