

Project Name

Location

Prepared By



## NUVO 60-7755

TEAGON 1 LIGHT WALL SCNCE

**Notes**

[www] 07-05-2023 01:10:03

**General**

Status	Active
Collection	Teagon
Finish	Polished Nickel
Style	Modern
Number of Lamps	1
Height (in.)	23.38
Width (in.)	8.00
Extension (in.)	7.63
Indoor or Outdoor Fixture	Indoor

**Specifications**

Base	Medium
Bulb Type	Incandescent
Max Wattage	60W
Bulb Included	No
Weight (lb.)	3.74
Up/Down Installation	Up or Down
Fixture Shape	Linear
Fixture Type	Wall Sconce
Fixture Material	Steel

**Dimensions**

Back Plate or Canopy Height (in.)	0.75
Back Plate or Canopy Diameter (in.)	5.00
Top to Outlet	8.00

**Compliance**

Safety Listing	cULus - Listed
Location Rating	Damp
Energy Star	No
DLC Approved	No
California Prop 65	Lead

**Additional Information**

Warranty	1 Year Limited - Fixtures
----------	---------------------------