

Project Name

Location

Prepared By



## NUVO 60-7757

TEAGON 1 LIGHT WALL SCONCE

### Notes

[www] 67-65-2023 01:10:03

### General

|                           |               |
|---------------------------|---------------|
| Status                    | Active        |
| Collection                | Teagon        |
| Finish                    | Natural Brass |
| Style                     | Modern        |
| Number of Lamps           | 1             |
| Height (in.)              | 23.38         |
| Width (in.)               | 8.00          |
| Extension (in.)           | 7.63          |
| Indoor or Outdoor Fixture | Indoor        |

### Specifications

|                      |              |
|----------------------|--------------|
| Base                 | Medium       |
| Bulb Type            | Incandescent |
| Max Wattage          | 60W          |
| Bulb Included        | No           |
| Weight (lb.)         | 3.74         |
| Up/Down Installation | Up or Down   |
| Fixture Shape        | Linear       |
| Fixture Type         | Wall Sconce  |
| Fixture Material     | Steel        |

### Dimensions

|                                     |      |
|-------------------------------------|------|
| Back Plate or Canopy Height (in.)   | 0.75 |
| Back Plate or Canopy Diameter (in.) | 5.00 |
| Top to Outlet                       | 8.00 |

### Compliance

|                    |                |
|--------------------|----------------|
| Safety Listing     | cULus - Listed |
| Location Rating    | Damp           |
| Energy Star        | No             |
| DLC Approved       | No             |
| California Prop 65 | Lead           |

### Additional Information

|          |                           |
|----------|---------------------------|
| Warranty | 1 Year Limited - Fixtures |
|----------|---------------------------|