

Project Name

Location

Prepared By



NUVO 60-7762

ROWEN 4 LIGHT SEMI FLUSH

Notes

[www] 07-05-2023 01:10:03

General

Status	Active
Collection	Rowen
Finish	Brushed Nickel
Style	Traditional
Number of Lamps	4
Height (in.)	11.13
Width (in.)	18.50
Indoor or Outdoor Fixture	Indoor

Specifications

Base	Medium
Bulb Type	Incandescent
Max Wattage	60W
Bulb Included	No
Glass Description	Etched White
Weight (lb.)	10.38
Fixture Shape	Bowl
Fixture Type	Semi Flush Mount
Fixture Material	Steel

Dimensions

Back Plate or Canopy Diameter (in.)	6.00
-------------------------------------	------

Compliance

Safety Listing	cULus - Listed
Location Rating	Damp
Energy Star	No
DLC Approved	No
California Prop 65	Lead

Additional Information

Warranty	1 Year Limited - Fixtures
----------	---------------------------