

Project Name

Location

Prepared By



NUVO 60-7766

ADINA 1 LIGHT MEDIUM PENDANT

Notes

[www] 67-65-2023 01:10:03

General

Status	Active
Collection	Adina
Finish	Matte Black
Style	Transitional
Number of Lamps	1
Height (in.)	13.75
Width (in.)	12.75
Indoor or Outdoor Fixture	Indoor

Specifications

Base	Medium
Bulb Type	Incandescent
Max Wattage	60W
Bulb Included	No
Weight (lb.)	4.29
Sloped Ceiling	Yes
Fixture Shape	Cone
Fixture Type	Pendant
Fixture Material	Steel

Dimensions

Back Plate or Canopy Height (in.)	3.00
Back Plate or Canopy Diameter (in.)	5.00
Stem Length	36 in.

Compliance

Safety Listing	cULus - Listed
Location Rating	Damp
Energy Star	No
DLC Approved	No
California Prop 65	Lead

Additional Information

Includes	(2) 6 inch Rods; (2) 12 inch Rods; (1) 12 foot Wire
Warranty	1 Year Limited - Fixtures