

Project Name

Location

Prepared By



## NUVO 60-7802

BOLIVER 3 LIGHT 11 PENDANT

### Notes

[www] 07-05-2023 01:10:03

### General

Status	Active
Collection	Boliver
Finish	Brushed Nickel
Style	Traditional
Number of Lamps	3
Height (in.)	24.00
Width (in.)	11.75
Indoor or Outdoor Fixture	Indoor

### Specifications

Base	Candelabra
Bulb Type	Incandescent
Max Wattage	60W
Bulb Included	No
Glass Description	Clear Seeded
Weight (lb.)	7.25
Sloped Ceiling	Yes
Fixture Shape	Um
Fixture Type	Pendant
Fixture Material	Steel

### Dimensions

Back Plate or Canopy Height (in.)	0.90
Back Plate or Canopy Diameter (in.)	4.75
Chain Length	48 in.

### Compliance

Safety Listing	cETLus - Listed
Location Rating	Dry
Energy Star	No
DLC Approved	No
California Prop 65	Lead

### Additional Information

Includes	(1) 48 inch Chain; (1) 12 foot Wire
Warranty	1 Year Limited - Fixtures