

Project Name

Location

Prepared By



NUVO 60-7816

AMADO 1 LIGHT 10 PENDANT

Notes

[www] 07-05-2023 01:10:03

General

Status	Active
Collection	Amado
Finish	Polished Nickel
Style	Transitional
Number of Lamps	1
Height (in.)	16.50
Width (in.)	10.00
Indoor or Outdoor Fixture	Indoor

Specifications

Base	Medium
Bulb Type	Incandescent
Max Wattage	60W
Bulb Included	No
Glass Description	Clear
Weight (lb.)	4.00
Sloped Ceiling	Yes
Fixture Shape	Bowl
Fixture Type	Pendant
Fixture Material	Steel

Dimensions

Back Plate or Canopy Height (in.)	1.10
Back Plate or Canopy Diameter (in.)	5.00
Chain Length	48 in.

Compliance

Safety Listing	cETLus - Listed
Location Rating	Dry
Energy Star	No
DLC Approved	No
California Prop 65	Lead

Additional Information

Includes	(1) 48 inch Chain; (1) 12 foot Wire
Warranty	1 Year Limited - Fixtures