

Project Name

Location

Prepared By



## NUVO 60-7823

AMADO 3 LIGHT SEMI FLUSH MOUNT

### Notes

[www] 07-05-2023 01:10:03

### General

Status	Active
Collection	Amado
Finish	Matte Black
Style	Transitional
Number of Lamps	3
Height (in.)	14.25
Width (in.)	14.00
Indoor or Outdoor Fixture	Indoor

### Specifications

Base	Candelabra
Bulb Type	Incandescent
Max Wattage	60W
Bulb Included	No
Glass Description	Clear
Weight (lb.)	6.13
Fixture Shape	Bowl
Fixture Type	Semi Flush Mount
Fixture Material	Steel

### Dimensions

Back Plate or Canopy Height (in.)	1.00
Back Plate or Canopy Diameter (in.)	7.00

### Compliance

Safety Listing	cETLus - Listed
Location Rating	Dry
Energy Star	No
DLC Approved	No
California Prop 65	Lead

### Additional Information

Warranty	1 Year Limited - Fixtures
----------	---------------------------