

Project Name

Location

Prepared By



Notes

[www] 07-05-2023 01:10:03

General

Status	Active
Collection	Brookside
Finish	Vintage Brass
Style	Traditional
Number of Lamps	6
Height (in.)	12.25
Width (in.)	25.00
Length (in.)	42.00
Indoor or Outdoor Fixture	Indoor

Specifications

Base	Candelabra
Bulb Type	Incandescent
Max Wattage	60W
Bulb Included	No
Glass Description	Clear
Fabric Description	Glass
Weight (lb.)	14.25
Sloped Ceiling	Yes
Fixture Type	Island Pendant
Fixture Material	Steel

Dimensions

Back Plate or Canopy Length (in.)	14.00
Back Plate or Canopy Width (in.)	4.75
Back Plate or Canopy Height (in.)	1.00
Stem Length	36 in.

Compliance

Safety Listing	cETLus - Listed
Location Rating	Dry
Energy Star	No
DLC Approved	No
California Prop 65	Lead

Additional Information

Includes	(4) 6 inch Rods; (4) 12 inch Rods; (1) 12 foot Wire
Warranty	1 Year Limited - Fixtures