

Project Name

Location

Prepared By



NUVO 60-8041

ROSELLE 1 LIGHT VANITY

Notes

(revised) 08-28-2024 01:06:09

General

Status	Active
Collection	Roselle
Finish	Natural Brass
Style	Contemporary
Number of Lamps	1
Height (in.)	13.75
Width (in.)	4.5
Extension (in.)	5.75
Indoor or Outdoor Fixture	Indoor

Specifications

Base	Medium
Bulb Type	Lamp Dependent
Max Wattage	60W
Voltage	120V
Bulb Included	No
Dimmable	Lamp Dependent
Glass Description	White
Fabric Description	White
Weight (lb.)	3.54
Sloped Ceiling	No
Up/Down Installation	Universal
Fixture Shape	Round
Fixture Type	Vanity
Fixture Material	Steel

Dimensions

Back Plate or Canopy Length (in.)	4.5
Back Plate or Canopy Width (in.)	0.75
Back Plate or Canopy Height (in.)	6.88
Top to Outlet	10.38

Compliance

Safety Listing	cETLus
Location Rating	Damp
ADA Compliant	No
CA T20 / T24 Rationale	T20 Exempt - Fixtures Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Warranty	1 Year Limited - Fixtures
----------	---------------------------