

Project Name

Location

Prepared By



Notes

[www] 08-28-2024 01:00:00

General

Status	Active
Collection	Broadstone
Finish	Matte Black
Style	Transitional
Number of Lamps	2
Height (in.)	15.63
Width (in.)	7
Extension (in.)	9
Indoor or Outdoor Fixture	Outdoor

Specifications

Base	Candelabra
Bulb Type	Lamp Dependent
Max Wattage	40W
Voltage	120V
Bulb Included	No
Dimmable	Lamp Dependent
Glass Description	Clear Seeded
Fabric Description	Clear Seeded
Weight (lb.)	6.8
Sloped Ceiling	No
Up/Down Installation	Down
Fixture Shape	Cylinder
Fixture Type	Wall Lantern
Fixture Material	Die-Cast Aluminum / Glass

Dimensions

Back Plate or Canopy Length (in.)	4.5
Back Plate or Canopy Height (in.)	6.5
Top to Outlet	2.5

Compliance

Safety Listing	cETLus - Listed
Location Rating	Wet
ADA Compliant	No
CA T20 / T24 Rationale	T20 Exempt - Fixtures Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Warranty	1 Year Limited - Fixtures
----------	---------------------------