

Project Name

Location

Prepared By



Notes

[www] 07-20-2020 00:51:21

General

Status	Active
Finish	White
Wattage	15
Style	Contemporary
CCT (Kelvin)	4000
Color Temperature	Cool White
Width (in.)	7.09
Height (in.)	1.18

Specifications

Technology	LED
CRI	90
Lumen Output	1500
Rated Hours	50000
Voltage	120V
Dimmable	Yes Dimmable
Weight (lb.)	0.51
Fixture Shape	Round
Fixture Type	Disk Light

Compliance

Safety Listing	cETLus
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2357896
CA Prop 65	Lead
RoHS Compliant	Yes

Additional Information

Additional Information	60 Watt equivalent
Warranty	5 Year Limited