

Project Name

Location

Prepared By



**Notes**

[www] 07-05-2023 01:10:03

**General**

Status	Active
Collection	Kagen
Finish	Brushed Nickel
Wattage	26W
Style	Contemporary
CCT (Kelvin)	3000K
Color Temperature	Warm White
Width (in.)	25.58
Height (in.)	5.00
Extension (in.)	3.25
Indoor or Outdoor Fixture	Indoor

**Smart Product Info**

IOT Enabled	No
-------------	----

**Specifications**

Technology	LED
CRI	90
Lumen Output	2080L
Rated Hours	30000
Voltage	120V
Dimmable	Yes_Dimmable
Weight (lb.)	2.82
Up/Down Installation	Up or Down
Fixture Material	Steel
Fixture Type	Vanity

**Dimensions**

Back Plate or Canopy Diameter (in.)	5.00
-------------------------------------	------

**Compliance**

Safety Listing	cETLus - Listed
Location Rating	Damp
Energy Star	No
DLC Approved	No
California Prop 65	Lead
SDS Sheet	LED_Fixture

**Additional Information**

Warranty	3 Year Limited - Fixtures
----------	---------------------------