

Project Name

Location

Prepared By



NUVO 62-1746

BLINK LED 7" ROUND 11W 0-10V

Notes

[www] 06-12-2024 03:11:00

General

Status	Active
Fixture Type	Flush Mount
Finish	White
Wattage	11W
Lumen Output	980L
CCT (Kelvin)	3000K
Indoor or Outdoor Fixture	Indoor; Outdoor

Specifications

Technology	LED
Color Temperature	Soft White
CRI	90
Voltage	120V/277V
Beam Angle	100
Rated Hours	50000
Operating Temperature	-25C (-13F) to +40C (+104F)
Dimmable	Yes-Dimmable
Dimming Note	0-10V Dimming
Lens Material	Polycarbonate (PC)
Surge Protection	Built-in surge protection - 2.5KV
Weight (lb.)	0.9
Material	Aluminum

Dimensions

Height (in.)	0.67
Width (in.)	7

Compliance

Safety Listing	cETLus - Listed
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2386777
DLC Approved	No
CA T20 / T24 Rationale	California T24 2016 - 2022 JA8 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Warranty	5 Year Limited - Fixtures
----------	---------------------------