

Project Name

Location

Prepared By



Notes

[www] 05-01-2023 02:04:54

General

Status	Active
Finish	Brushed Nickel
Wattage	18W
Style	Contemporary
CCT (Kelvin)	3000K
Color Temperature	Warm White
Width (in.)	11.75
Height (in.)	4.50

Specifications

Technology	LED
CRI	90+
Lumen Output	1500L
Rated Hours	50000
Voltage	120V/277V
Dimmable	Yes-Dimmable
Glass Description	Frost
Weight (lb.)	2.77
Fixture Material	Glass
Fixture Type	Flush Mount
Operating Temperature	-17C (+1.4F) to +45C (+113F)

Compliance

Safety Listing	cETLus - Listed
Location Rating	Damp
CA T20 / T24 Rationale	T20 Exempt - Fixtures Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Additional Information	Twist & Lock
Warranty	5 Year Limited - Fixtures