

Project Name

Location

Prepared By



# NUVO 65-572R1

2X4 LED BACKLIT FLAT PANEL

## Notes

[www] 06-17-2023 22:42:03

## General

|                           |                    |
|---------------------------|--------------------|
| Status                    | Active             |
| Fixture Type              | Backlit Flat Panel |
| Finish                    | White              |
| Wattage                   | 30W/40W/50W        |
| Lumen Output              | 3300L-5750L        |
| CCT (Kelvin)              | 3500K/4000K/5000K  |
| IP Rating                 | IP20               |
| Indoor or Outdoor Fixture | Indoor             |

## Smart Product Info

|             |    |
|-------------|----|
| IOT Enabled | No |
|-------------|----|

## Specifications

|                       |                                 |
|-----------------------|---------------------------------|
| Technology            | LED                             |
| Color Temperature     | Warm to Cool White              |
| CRI                   | 80+                             |
| Voltage               | 100V-277V                       |
| Beam Angle            | 120                             |
| Rated Hours           | 50000                           |
| Operating Temperature | -17C (+1.4F) to +45C (+113F)    |
| Dimmable              | Yes-Dimmable                    |
| Dimming Note          | 0-10V Dimming Only              |
| Photocell or Sensor   | No Photocell                    |
| Lens Material         | Poly methyl methacrylate (PMMA) |
| Surge Protection      | Built-in surge protection - 2KV |
| Weight (lb.)          | 9.04                            |
| Material              | Aluminum / Steel                |

## Dimensions

|              |       |
|--------------|-------|
| Height (in.) | 1.5   |
| Width (in.)  | 23.75 |
| Length (in.) | 47.72 |

## Compliance

|                        |                                     |
|------------------------|-------------------------------------|
| Safety Listing         | cETLus                              |
| Location Rating        | Damp                                |
| Energy Star            | No                                  |
| DLC Approved           | Yes                                 |
| DLC ID                 | S-QJAOE2                            |
| NSF Approved           | Yes                                 |
| Air Tight Rated        | No                                  |
| IC Rated               | Yes                                 |
| CA T20 / T24 Rationale | T20 Exempt - Fixtures Not Regulated |
| California Status      | Lawful for sale in California       |
| Title 20 / 24 Status   | Lawful for sale                     |
| California Prop 65     | Lead                                |
| RoHS Compliant         | Yes                                 |
| FCC Compliant          | Yes                                 |
| Flicker Free           | Yes                                 |
| SDS Sheet              | LED_Fixture                         |

## Additional Information

Additional Information

Driver Specs - VDC38-48V;  
630/810/1030mA

Warranty

5 Year Limited - Fixtures

Copyright 2020 Satco Products, Inc.  
All Rights Reserved

For More Information Visit:  
<http://www.satco.com/>

