

Project Name

Location

Prepared By



SATCO S11239

5W/LED/G9/850/CL/120V/DIM

Notes

[www] 05-15-2024 04:42:54

General

Status	Active
Watts	5W
HID Equivalent	40W
Volts	120V
Shape	T4
Base	G9 Double Loop
ANSI Base	G9
Finish	Clear
CCT (Kelvin)	5000K
Temperature	Natural Light
CRI	80
Lumens	550L
Beam Spread	300
Dimmable	Yes-Dimmable
Hours Rated	25000
Product Category	LED
Technology	LED

Electrical

Operating Frequency	60Hz
Operating Temperature	-20C (-4F) to +40C (+104F)

Physical

MOL	2.13
MOD	0.75
Weight (lb.)	0.06

Additional Information

Installation Notes	Not for use in vapor tight fixtures. For proper ventilation, original protective glass shield for halogen lamps should be removed during installation.
Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - Mini LED Pin Base

Compliance

Safety Listing	cULus - Listed
Location Rating	Damp
Energy Star	No
CA T20 / T24 Rationale	Exempt - Base Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes
SDS Sheet	LED_Lamp