

Project Name

Location

Prepared By



SATCO S11284

12BR40/LED/RGB/TW/T20/SF

Notes

[www] 02-26-2020 02:59:17

General

Status	Active
Watts	12W
Incandescent Equivalent	75W
Volts	120V
Shape	BR40
Base	Medium
ANSI Base	E26
Finish	White
CCT (Kelvin)	2700K-5000K
Temperature	Warm to Cool White/Color Changeable
CRI	90
Lumens	960L
Beam Spread	110
Dimmable	Yes-Dimmable
Hours Rated	25000
Lamp Type	Reflector
Technology	LED

Smart Product Info

IOT Enabled	Yes
Voice Assistants Supported	Siri Shortcuts; Alexa; Hey Google; SmartThings

Specifications

Dimming Note	Only with Starfish App; Dimming range from 100 to less than or equal to 20 percent depending on dimmer control
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical

MOL	6.42
MOD	4.72
Weight (lb.)	0.29

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - 3 hr per day

Compliance

Safety Listing	cULus - Listed
Location Rating	Damp
Energy Star	Pending
CA T20 / T24 Rationale	T20 Compliant
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp

