

Project Name

Location

Prepared By



## SATCO S11293

9WLED/GBL/4/RGBW/RND/WH

### Notes

[www] 11-01-2023 00:12:53

### General

Status	Active
Wattage	9W
Voltage	120V-277V
Finish	White
CCT (Kelvin)	2700K-5000K
Color Temperature	Warm to Cool White\Color Changeable
Lumen Output	650L
Indoor or Outdoor Fixture	Indoor

### Specifications

Technology	LED
CRI	90
Beam Angle	36
Rated Hours	50000
Operating Temperature	-20C (-4F) to +45C (+113F)
Dimmable	Yes-Dimmable
Dimming Note	Only with Starfish App

### Dimensions

Width (in.)	4.92
Height (in.)	1.44
Weight (lb.)	0.99

### Compliance

Safety Listing	cETLus - Listed
Location Rating	Damp
Energy Star	Yes
ES Unique ID	ESID-2470769
Air Tight Rated	Yes
IC Rated	Yes
CA T20 / T24 Rationale	California T24 2016 - 2022 JA8 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	California T24 Listed
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Fixture

### Additional Information

Specification Note	360 degree rotation; 0 to 80 degree aiming angle
Warranty	5 Year Limited - Fixtures