

Project Name

Location

Prepared By



**Notes**

[www] 11-01-2023 00:12:53

**General**

Status	Active
Wattage	15W
Voltage	120V-277V
Finish	White
CCT (Kelvin)	2700K-5000K
Color Temperature	Warm to Cool White\Color Changeable
Lumen Output	1200L
Indoor or Outdoor Fixture	Indoor

**Specifications**

Technology	LED
CRI	90
Beam Angle	36
Rated Hours	50000
Operating Temperature	-20C (-4F) to +45C (+113F)
Dimmable	Yes-Dimmable
Dimming Note	Only with Starfish App

**Dimensions**

Width (in.)	7.48
Height (in.)	2.13
Weight (lb.)	1.22

**Compliance**

Safety Listing	cETLus - Listed
Location Rating	Damp
Energy Star	Yes
ES Unique ID	ESID-2470770
Air Tight Rated	Yes
IC Rated	Yes
CA T20 / T24 Rationale	California T24 2016 - 2022 JA8 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	California T24 Listed
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Fixture

**Additional Information**

Specification Note	360 degree rotation; 0 to 80 degree aiming angle
Warranty	5 Year Limited - Fixtures