

Project Name

Location

Prepared By



SATCO S11321

5.5A19/LED/930/120V/D

Notes

[www] 08-10-2020 02:07:42

General

Status	Active
Watts	5.5
Incandescent Equivalent	40
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	White
CCT (Kelvin)	3000
Temperature	Warm White
CRI	90+
Lumens	450
Beam Spread	220
Dimmable	Yes - Dimmable
Hours Rated	25000
Lamp Type	Type A
Technology	LED

Electrical

Operating Frequency	60 Hz
Dimming Type	Forward Phase & Reverse Phase
Power Factor	0.92
Operating Temperature	-25C (-13F) to a maximum of +45C (+113F)

Physical

MOL	4.33
MOD	2.36
Housing Color	White
Weight (lb.)	0.095

Additional Information

Enclosure Rating	Enclosed Rated Lamp
Rated For Enclosed Fixture	Yes
Warranty	5 Year Limited - 10 hr per day

Compliance

Safety Listing	cETLus
Location Rating	Damp
Energy Star	Pending
CEC Status	California T24 Compliant
RoHS Compliant	Yes
SDS Sheet	LED_Lamp