

Project Name

Location

Prepared By



SATCO S11332

20A21/LED/950/120-277V/ND

Notes

[www] 09-10-2020 02:07:42

General

Status	Active
Watts	20
Incandescent Equivalent	125
Fluorescent Equivalent	32W
Volts	120V-277V
Shape	A21
Base	Medium
ANSI Base	E26
Finish	White
CCT (Kelvin)	5000
Temperature	Natural Light
CRI	90+
Lumens	2000
Beam Spread	220
Dimmable	Non-Dimmable
Hours Rated	25000
Lamp Type	Type A
Technology	LED

Electrical

Operating Frequency	60 Hz
Power Factor	0.94 / 0.8
Operating Temperature	-25C (-13F) to a maximum of +45C (+113F)

Physical

MOL	5.55
MOD	2.63
Housing Color	White
Weight (lb.)	0.337

Additional Information

Additional Info	120V:0.94, 277V:0.87
Enclosure Rating	Enclosed Rated Lamp
Rated For Enclosed Fixture	Yes
Warranty	5 Year Limited - 10 hr per day

Compliance

Safety Listing	cULus - Listed
Location Rating	Damp
Energy Star	No
CEC Status	Lawful for sale in California
RoHS Compliant	Yes
SDS Sheet	LED_Lamp