

Project Name

Location

Prepared By



SATCO S11346

8W/CTF/LED/930/120V/E12

Notes

[www] 01-15-2024 02:40:00

General

Status	Active
Watts	8W
Incandescent Equivalent	75W
Volts	120V
Shape	C11
Base	Candelabra
ANSI Base	E12
Finish	Frost
CCT (Kelvin)	3000K
Temperature	Soft White
CRI	90
Lumens	760L
Beam Spread	300
Dimmable	Yes-Dimmable
Dimming Note	120V only
Hours Rated	15000
Lamp Type	Candle
Technology	LED

Smart Product Info

IOT Enabled	No
-------------	----

Electrical

Operating Frequency	60Hz
Operating Position	Universal
Operating Temperature	-20C (-4F) to +45C (+113F)

Physical

MOL	3.86
MOD	1.38
Weight (lb.)	0.05

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - 4 hr per day

Compliance

Safety Listing	cULus - Listed
Location Rating	Damp
Energy Star	No
CA T20 / T24 Rationale	T20 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
IP Rating	IP20
RoHS Compliant	Yes
SDS Sheet	LED_Lamp