

Project Name

Location

Prepared By



SATCO S11355

8A19/LED/930/CL/120V

Notes

[www] 08-31-2020 01:09:31

General

Status	Active
Watts	8
Incandescent Equivalent	60
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	Clear
CCT (Kelvin)	3000
Temperature	Warm White
CRI	90
Lumens	800
Beam Spread	360
Dimmable	Yes - Dimmable
Hours Rated	15000
Lamp Type	Type A
Technology	LED

Electrical

Operating Frequency	60 Hz
Dimming Type	Forward
Power Factor	0.9
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical

MOL	4.3
MOD	2.36
Weight (lb.)	0.08

Additional Information

Enclosure Rating	Enclosed Rated Lamp
Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	Yes
ES Unique ID	ESID-2362840
CEC Status	California T24 Compliant
RoHS Compliant	Yes
SDS Sheet	LED_Lamp