

Project Name

Location

Prepared By



## SATCO S11360

14A21/LED/927/CL/120V

### Notes

[www] 08-31-2020 01:09:31

### General

Status	Active
Watts	14
Incandescent Equivalent	100
Volts	120V
Shape	A21
Base	Medium
ANSI Base	E26
Finish	Clear
CCT (Kelvin)	2700
Temperature	Warm White
CRI	90
Lumens	1600
Beam Spread	360
Dimmable	Yes - Dimmable
Hours Rated	15000
Lamp Type	Type A
Technology	LED

### Electrical

Operating Frequency	60 Hz
Dimming Type	Forward
Power Factor	0.9
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

### Physical

MOL	5.0
MOD	2.76
Weight (lb.)	0.12

### Additional Information

Enclosure Rating	Enclosed Rated Lamp
Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

### Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	Yes
ES Unique ID	ESID-2362940
CEC Status	California T24 Compliant
RoHS Compliant	Yes
SDS Sheet	LED_Lamp