Project Name

Location | Prepared By



SATCO S11378

8BT15/LED/927/CL/120V

Notes

[www] 08-31-2020 01:09:31

General	
Status	Active
Watts	8
Incandescent Equivalent	60
Volts	120V
Shape	BT15
Base	Medium
ANSI Base	E26
Finish	Clear
CCT (Kelvin)	2700
Temperature	Warm White
CRI	90
Lumens	800
Beam Spread	360
Dimmable	Yes - Dimmable
Hours Rated	15000
Lamp Type	BT
Technology	LED

Electrical	
Operating Frequency	60 Hz
Dimming Type	Forward
Power Factor	0.9
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical	
MOL	4.3
MOD	1.81
Weight (lb.)	0.08

Additional Information	
Enclosure Rating	Enclosed Rated Lamp
Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

Compliance	
Safety Listing	cULus
Location Rating	Damp
Energy Star	No
CEC Status	California T24 Compliant
RoHS Compliant	Yes
SDS Sheet	LED_Lamp

Copyright 2020 Satco Products, Inc.
All Rights Reserved

For More Information Visit:
https://www.satco.com/