

Project Name

Location

Prepared By



Notes

[www] 11-20-2023 01:02:46

General

Status	Active
Watts	4.5W
Incandescent Equivalent	35W
Volts	12V
Shape	MR16
Base	Bi Pin GU5.3
ANSI Base	GU5.3
Finish	Gray
CCT (Kelvin)	3000K
Temperature	Soft White
CRI	80
Lumens	360L
Beam Spread	15
Dimmable	Yes-Dimmable
Dimming Note	Check the transformer/driver MFG for dimmer compatibility
Hours Rated	25000
Lamp Type	MR
Technology	LED

Electrical

Operating Frequency	60Hz
CBCP	3000
Power Factor	0.94
Operating Temperature	-25C (-13F) to +45C (+113F)

Physical

MOL	1.77
MOD	1.97
Lensed	Lensed Lamp
Lens Finish	Array
Lens Material	Plastic
Housing Color	Gray
Weight (lb.)	0.08

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	5 Year Limited - 10 hr per day

Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	No
CA T20 / T24 Rationale	T20 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp



