

Project Name

Location

Prepared By



**Notes**

[www] 11-20-2023 01:02:46

**General**

|                         |   |
|-------------------------|---|
| Status                  | Active  |
| Watts                   | 6.5W  |
| Incandescent Equivalent | 50W   |
| Volts                   | 12V   |
| Shape                   | MR16  |
| Base                    | Bi Pin GU5.3  |
| ANSI Base               | GU5.3   |
| Finish                  | Black   |
| CCT (Kelvin)            | 5000K   |
| Temperature             | Natural Light   |
| CRI                     | 80  |
| Lumens                  | 500L  |
| Beam Spread             | 40  |
| Dimmable                | Yes-Dimmable  |
| Dimming Note            | Check the transformer/driver MFG for dimmer compatibility |
| Hours Rated             | 25000   |
| Lamp Type               | MR  |
| Technology              | LED   |

**Electrical**

|                       |                             |
|-----------------------|-----------------------------|
| Operating Frequency   | 60Hz                        |
| CBCP                  | 1060                        |
| Candlepower           | 1060                        |
| Power Factor          | 0.93                        |
| Operating Temperature | -25C (-13F) to +45C (+113F) |

**Physical**

|               |             |
|---------------|-------------|
| MOL           | 1.77        |
| MOD           | 1.97        |
| Lensed        | Lensed Lamp |
| Lens Finish   | Array       |
| Lens Material | Plastic     |
| Housing Color | Black       |
| Weight (lb.)  | 0.08        |

**Additional Information**

|                            |                                |
|----------------------------|--------------------------------|
| Rated For Enclosed Fixture | Yes                            |
| Warranty                   | 5 Year Limited - 10 hr per day |

**Compliance**

|                        |                               |
|------------------------|-------------------------------|
| Safety Listing         | cULus                         |
| Location Rating        | Damp                          |
| Energy Star            | No                            |
| CA T20 / T24 Rationale | T20 Listed                    |
| California Status      | Lawful for sale in California |
| Title 20 / 24 Status   | Lawful for sale               |
| RoHS Compliant         | Yes                           |
| FCC Compliant          | Yes                           |
| SDS Sheet              | LED_Lamp                      |



