

Project Name

Location

Prepared By



SATCO S11447

14A19/LED/827/120V/100PK

Notes

[www] 11-20-2023 01:02:46

General

Status	Active
Watts	14W
Incandescent Equivalent	100W
Fluorescent Equivalent	23W
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	Frost
CCT (Kelvin)	2700K
Temperature	Warm White
CRI	80
Lumens	1520L
Beam Spread	220
Dimmable	Non-Dimmable
Hours Rated	10000
Lamp Type	Type A
Technology	LED

Electrical

Operating Frequency	60Hz
Power Factor	0.5
Operating Temperature	-20C (-4F) to +45C (+113F)

Physical

MOL	4.38
MOD	2.38
Housing Color	White
Weight (lb.)	0.06

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - 10 hr per day

Compliance

Safety Listing	cULus - Listed
Location Rating	Damp
Energy Star	No
CA T20 / T24 Rationale	Non-Compliant - <82 CRI
California Status	Non-Compliant
Title 20 / 24 Status	Non-Compliant
RoHS Compliant	Yes
SDS Sheet	LED_Lamp