

Project Name

Location

Prepared By



## SATCO S11448

14A19/LED/840/120V/100PK

### Notes

[www] 11-20-2023 01:02:46

### General

|                         |              |
|-------------------------|--------------|
| Status                  | Active       |
| Watts                   | 14W          |
| Incandescent Equivalent | 100W         |
| Fluorescent Equivalent  | 23W          |
| Volts                   | 120V         |
| Shape                   | A19          |
| Base                    | Medium       |
| ANSI Base               | E26          |
| Finish                  | Frost        |
| CCT (Kelvin)            | 4000K        |
| Temperature             | Cool White   |
| CRI                     | 80           |
| Lumens                  | 1520L        |
| Beam Spread             | 220          |
| Dimmable                | Non-Dimmable |
| Hours Rated             | 10000        |
| Lamp Type               | Type A       |
| Technology              | LED          |

### Electrical

|                       |                            |
|-----------------------|----------------------------|
| Operating Frequency   | 60Hz                       |
| Power Factor          | 0.5                        |
| Operating Temperature | -20C (-4F) to +45C (+113F) |

### Physical

|               |       |
|---------------|-------|
| MOL           | 4.38  |
| MOD           | 2.38  |
| Housing Color | White |
| Weight (lb.)  | 0.065 |

### Additional Information

|                            |                                |
|----------------------------|--------------------------------|
| Rated For Enclosed Fixture | Yes                            |
| Warranty                   | 3 Year Limited - 10 hr per day |

### Compliance

|                        |                         |
|------------------------|-------------------------|
| Safety Listing         | cULus - Listed          |
| Location Rating        | Damp                    |
| Energy Star            | No                      |
| CA T20 / T24 Rationale | Non-Compliant - <82 CRI |
| California Status      | Non-Compliant           |
| Title 20 / 24 Status   | Non-Compliant           |
| RoHS Compliant         | Yes                     |
| SDS Sheet              | LED_Lamp                |