



S11454

13A19/LED/827/120V/D/4PK

GENERAL SPECIFICATIONS

Shape:	A19
Wattage:	13W
Lumen Output:	1100LL
Color Temperature:	2700K
Base:	Medium



TECHNICAL SPECIFICATIONS

Wattage:	13W
Volts:	120V
Incandescent Equivalent:	75W
Shape:	A19
Filament:	LED
Base:	Medium
ANSI Base:	E26
Finish:	Frost
Housing Color:	White
Hours Rated:	15000H
Color Temperature:	2700K

CRI:	80CRI
Lumen Output:	1100L
Dimmable:	Yes-Dimmable
Dimming Function:	Dimming range from 100 to less than or equal to 20 percent depending on dimmer control
Beam Spread:	230D
Operating Temp:	-20C (-4F) to a maximum of +45C (+113F)
Enclosure Rating:	Enclosed Rated Lamp
Safety Listing:	cULus - Listed
Technology:	LED
Material:	Polycarbonate (PC) / High Heat Conductive Plastic Housing

DIMENSIONS

MOL:	4.56"
MOD:	2.38"
Weight:	0.49

LISTINGS

Safety Listing:	cULus - Listed
Location Rating:	Damp
Energy Star:	Pending
UL File Listing:	US&CN E335148
FCC Compliant:	Yes
RoHS Compliant:	Yes
SDS Class:	LED_Lamp

PACKAGING

Each UPC:	045923114540
Each Quantity:	1
Each Dimensions:	7.24 x 2.44 x 4.92"

Case UPC:	10045923114547
Case Quantity:	12
Case Dimensions:	15.16 x 7.48 x 10.43"

110 Heartland Blvd.
Brentwood, NY 11717
PH 631-243-2022
FX 631-243-2027

Distribution Centers
New York, Florida,
Texas, Washington,
California, Puerto Rico

National Toll-Free
800-43-SATCO
(800-437-2826)
www.satco.com

Copyright 2022
Satco Products, Inc.
All Rights Reserved
March 30, 2022