

Project Name

Location

Prepared By



SATCO S11459

10.5A19/LED/850/AGRI/120V/D

Notes

[www] 05-08-2023 01:24:11

General

Status	Active
Watts	10.5W
Incandescent Equivalent	100W
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	White
CCT (Kelvin)	5000K
Temperature	Natural Light
CRI	80
Lumens	1600L
Beam Spread	140
Dimmable	Yes-Dimmable
Hours Rated	25000
Lamp Type	Type A
Technology	LED

Electrical

Operating Frequency	60Hz
Dimming Note	120V only
Power Factor	0.9
Operating Temperature	-20C (-4F) to +45C (+113F)

Physical

MOL	4.61
MOD	2.36
Housing Color	White
Weight (lb.)	0.14

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - 16 hr per day

Compliance

Safety Listing	cULus - Listed
Location Rating	Wet
Energy Star	No
Air Tight Rated	No
CA T20 / T24 Rationale	Non-Compliant - <82 CRI
California Status	Non-Compliant
Title 20 / 24 Status	Non-Compliant
RoHS Compliant	Yes