

Project Name

Location

Prepared By



IMAGE NOT AVAILABLE

# SATCO S11478

5B11/DUSK/DAWN/950

**Notes**

[www] 06-07-2023 00:27:23

**General**

Status	Active
Watts	5W
Incandescent Equivalent	60W
Volts	120V
Shape	B11
Base	Candelabra
ANSI Base	E12
Finish	White
CCT (Kelvin)	5000K
Temperature	Natural Light
CRI	90
Lumens	500L
Beam Spread	280
Dimmable	Non-Dimmable
Hours Rated	15000
Lamp Type	Candle
Technology	LED

**Smart Product Info**

IOT Enabled	No
-------------	----

**Electrical**

Operating Frequency	60Hz
Power Factor	0.7
Operating Position	Universal
Operating Temperature	-20C (-4F) to +40C (+104F)

**Physical**

MOL	4.02
MOD	1.38
Photocell or Sensor	Has Photocell
Weight (lb.)	0.08

**Additional Information**

Rated For Enclosed Fixture	No
Warranty	3 Year Limited

**Compliance**

Safety Listing	cULus - Listed
Location Rating	Damp
Energy Star	No
CA T20 / T24 Rationale	T20 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes

