

Project Name

Location

Prepared By



SATCO S11494

7PAR20/LED/35°/930/120-277V

Notes

[www] 01-15-2024 02:40:00

General

Status	Active
Watts	7W
Incandescent Equivalent	50W
Volts	120V-277V
Shape	PAR20
Base	Medium
ANSI Base	E26
Finish	Silver
CCT (Kelvin)	3000K
Temperature	Soft White
CRI	90
Lumens	450L
Beam Spread	35
Dimmable	Non-Dimmable
Hours Rated	15000
Lamp Type	PAR
Technology	LED

Electrical

Operating Frequency	60Hz
CBCP	750
Power Factor	0.9
Operating Temperature	-20C (-4F) to +40C (+104F)

Physical

MOL	3.27
MOD	2.52
Lens Finish	Clear
Lens Material	Polycarbonate (PC)
Housing Color	Silver
Weight (lb.)	0.21

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - 10 hr per day

Compliance

Safety Listing	cULus
Location Rating	Wet
CA T20 / T24 Rationale	T20 Pending
RoHS Compliant	Yes
FCC Compliant	Yes