

Project Name

Location

Prepared By

**SATCO S11522**

6G25/CL/LED-GF/COIL/927/120V

Notes

(revised) 07-31-2024 01:33:49

General

Status	Active
Watts	6W
Incandescent Equivalent	60W
Volts	120V
Shape	G25
Base	Medium
ANSI Base	E26
Finish	Clear
CCT (Kelvin)	2700K
Temperature	Warm White
CRI	93
Lumens	500L
Beam Spread	360
Dimmable	Yes-Dimmable
Dimming Note	120V only
Hours Rated	15000
Technology	LED

Smart Product Info

Start Up	0.5s
----------	------

Electrical

Operating Frequency	60Hz
Power Factor	0.7
Operating Temperature	-20C (-4F) to +45C (+113F)

Physical

MOL	4.72
MOD	3.15
Weight (lb.)	0.09

Additional Information

Rated For Enclosed Fixture	Yes
Installation Notes	Can be used outdoors only when in an enclosed fixture
Warranty	3 Year Limited

Compliance

Safety Listing	cULus - Listed
Location Rating	Damp
Energy Star	No
CA T20 / T24 Rationale	T20 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
IP Rating	IP65
RoHS Compliant	Yes