

Project Name

Location

Prepared By

**SATCO S11524**

6T9/CL/LED-GF/COIL/927/120V

**Notes**

(revised) 07-31-2024 01:33:49

**General**

|                         |              |
|-------------------------|--------------|
| Status                  | Active       |
| Watts                   | 6W           |
| Incandescent Equivalent | 40W          |
| Volts                   | 120V         |
| Shape                   | T9           |
| Base                    | Medium       |
| ANSI Base               | E26          |
| Finish                  | Clear        |
| CCT (Kelvin)            | 2700K        |
| Temperature             | Warm White   |
| CRI                     | 93           |
| Lumens                  | 500L         |
| Beam Spread             | 360          |
| Dimmable                | Yes-Dimmable |
| Dimming Note            | 120V only    |
| Hours Rated             | 15000        |
| Technology              | LED          |

**Smart Product Info**

|          |      |
|----------|------|
| Start Up | 0.5s |
|----------|------|

**Electrical**

|                       |                            |
|-----------------------|----------------------------|
| Operating Frequency   | 60Hz                       |
| Power Factor          | 0.7                        |
| Operating Temperature | -20C (-4F) to +45C (+113F) |

**Physical**

|              |      |
|--------------|------|
| MOL          | 7.48 |
| MOD          | 1.18 |
| Weight (lb.) | 0.09 |

**Additional Information**

|                            |                                                       |
|----------------------------|-------------------------------------------------------|
| Rated For Enclosed Fixture | Yes                                                   |
| Installation Notes         | Can be used outdoors only when in an enclosed fixture |
| Warranty                   | 3 Year Limited                                        |

**Compliance**

|                        |                               |
|------------------------|-------------------------------|
| Safety Listing         | cULus - Listed                |
| Location Rating        | Damp                          |
| Energy Star            | No                            |
| CA T20 / T24 Rationale | T20 Listed                    |
| California Status      | Lawful for sale in California |
| Title 20 / 24 Status   | Lawful for sale               |
| IP Rating              | IP65                          |
| RoHS Compliant         | Yes                           |