

Project Name

Location

Prepared By



SATCO S11553

5.5W/LED/CFL/840/2P/DUAL

Notes

[www] 09-14-2020 01:39:49

General

Status	Active
Watts	5.5
Volts	120V-277V
Ballast Type	Type A/B
Shape	PL
Base	GX23
ANSI Base	GX23
Finish	Frosted
CCT (Kelvin)	4000
Temperature	Cool White
CRI	80
Lumens	500
Beam Spread	120
Dimmable	Non-Dimmable
Hours Rated	50000
Lamp Type	PL 2-Pin
Technology	LED

Electrical

Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)
-----------------------	---

Physical

MOL	5.98
MOD	1.26
Weight (lb.)	0.13

Additional Information

Enclosure Rating	Open Rated Lamp
Warranty	5 Year Limited - 10 hr per day

Compliance

Safety Listing	cULus Listed for Type A; cULus Classified for Type B
Location Rating	Damp
Energy Star	No
CEC Status	Lawful for sale in California
RoHS Compliant	Yes
SDS Sheet	LED_Lamp