

Project Name

Location

Prepared By



Notes

[www] 11-01-2023 00:12:53

General

Status	Active
Finish	White
Wattage	13W
Style	Utility
CCT (Kelvin)	2000K-5000K
Color Temperature	Warm to Cool White\Color Changeable
Length (in.)	6.77
Width (in.)	6.77
Height (in.)	3.38
Indoor or Outdoor Fixture	Indoor

Smart Product Info

IOT Enabled	Yes
Voice Assistants Supported	Google Home;Alexa;Siri;SmartThings

Specifications

Technology	LED
CRI	90
Lumen Output	850L
Rated Hours	50000
Voltage	120V
Dimmable	Yes-Dimmable
Dimming Note	Only with Starfish App
Beam Angle	110
Operating Temperature	-20C (-4F) to +40C (+104F)
IC Rated	Yes
Weight (lb.)	0.97
Fixture Shape	Square
Fixture Material	Aluminum
Fixture Type	Downlight Retrofit

Compliance

Safety Listing	cETLus
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2495005
Air Tight Rated	Yes
CA T20 / T24 Rationale	California T24 2016 - 2022 JA8 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	California T24 Listed
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Fixture

Additional Information

Includes	E26 Adapter included (S9001)
Warranty	5 Year Limited - Fixtures

