

Project Name

Location

Prepared By



SATCO S11650

9T5/LED/24-CCT/BP/HE/SE-DE

Notes

[www] 05-15-2024 04:42:54

General

Status	Active
Watts	9W
Incandescent Equivalent	75W
Fluorescent Equivalent	14W
Volts	120V-277V
Ballast Type	Type B
Shape	T5
Base	Miniature Bi Pin
ANSI Base	G5
Nominal Length	24
Finish	White
CCT (Kelvin)	3000K/3500K/4000K/5000K/6500K
CRI	82
Lumens	1100L/1175L/1200L/1250L/1150L
Beam Spread	160
Hours Rated	50000
Product Category	Linear
Technology	LED

Electrical

Ballasting Requirements	Ballast Bypass
Operating Frequency	50/60Hz
Power Factor	>0.9
THD	<25%
Operating Temperature	-20C (-4F) to +45C (+113F)

Physical

MOL	22.17
MOD	0.88
Material	Plastic
Lens Finish	Frost
Lens Material	Glass
Housing Color	White
Weight (lb.)	0.2

Additional Information

Shatter-Proof Type	PET Coated
Tube Guard Use	No
Installation Notes	Not for use in vapor tight fixtures.
Rated For Enclosed Fixture	Yes
Warranty	5 Year Limited - T5 LED Bulbs - Ballast Bypass

Compliance

Safety Listing	cULus - Classified; cETLus - Listed; cRUus - Recognized Component
Location Rating	Damp
Energy Star	No
DLC Approved	No
CA T20 / T24 Rationale	Exempt - Base Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale

RoHS Compliant	Yes
FCC Compliant	Yes
NSF Approved	Yes
SDS Sheet	LED_Lamp

