

Project Name

Location

Prepared By



SATCO S11730

15T8/LED/48-CCT/BB/BP

Notes

[www] 05-15-2024 04:42:54

General

Status	Active
Watts	15W
Incandescent Equivalent	75W
Fluorescent Equivalent	32W
Volts	120V-277V
Ballast Type	Type B
Shape	T8
Base	Medium Bi Pin
ANSI Base	G13
Nominal Length	48
Finish	White
CCT (Kelvin)	3500K/4000K/5000K
CRI	83
Lumens	1850L/2000L/1900L
Beam Spread	140
Hours Rated	50000
Product Category	Linear
Technology	LED

Electrical

Ballasting Requirements	Ballast Bypass
Operating Frequency	60Hz
Power Factor	0.9
THD	<25%
Operating Temperature	-20C (-4F) to +45C (+113F)

Physical

MOL	47.78
MOD	1.13
Material	Aluminum
Lens Finish	Frost
Lens Material	Polycarbonate (PC)
Housing Color	White
Weight (lb.)	0.99

Additional Information

Additional Info	3.5 Watts and 500 Lumens in Emergency Mode
Shatter-Proof Type	Yes
Tube Guard Use	No
Installation Notes	Not for use in vapor tight fixtures. Maximum Mounting Height: 13 Feet
Specification Note	Height at switch: 1.30 Inches; Work time after power failure: 90 Minutes; Battery Recharge Time is 24 hours
Rated For Enclosed Fixture	Yes
Warranty	5 Year Limited - T8 LED Bulbs - Ballast Bypass

Compliance

Safety Listing	cULus - Classified; cETLus - Listed; cRUus - Recognized Component
----------------	---

Location Rating	Damp
Energy Star	No
DLC Approved	Yes
DLC ID	S-U53N8J
CA T20 / T24 Rationale	Exempt - Base Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
NSF Approved	Yes
SDS Sheet	LED_Lamp

