

Project Name

Location

Prepared By



**Notes**

[www] 01-15-2024 02:40:09

**General**

Status	Active
Watts	15W
Incandescent Equivalent	75W
Fluorescent Equivalent	55W
Volts	120V-277V
Ballast Type	Type A/B
Shape	T8
Base	Medium Bi Pin
ANSI Base	G13
Nominal Length	48
Finish	White
CCT (Kelvin)	3500K/4000K/5000K
Temperature	Neutral White to Natural Light
CRI	83
Lumens	2150L/2200L/2200L
Beam Spread	180
Dimmable	Yes-Dimmable
Hours Rated	50000
Lamp Type	Linear
Technology	LED

**Electrical**

Ballasting Requirements	Ballast required (Type A) or Ballast Bypass (Type B)
Operating Frequency	50/60Hz
Dimming Note	Only in Type A mode; Check Ballast MFG for Dimmer Compatibility
Power Factor	0.9
Operating Temperature	-20C (-4F) to +45C (+113F)

**Physical**

MOL	47.78
MOD	1
Material	Glass / Plastic
Lens Finish	Frost
Lens Material	Glass
Housing Color	White

**Additional Information**

Shatter-Proof Type	PET Coated
Rated For Enclosed Fixture	Yes
Warranty	5 Year Limited - T8 LED Bulbs

**Compliance**

Safety Listing	cULus - Listed; cULus - Classified; cETLus - Listed
Location Rating	Damp
Energy Star	No
DLC Approved	Yes
DLC ID	S-X87CKG
CA T20 / T24 Rationale	Exempt - Base Not Regulated
California Status	Lawful for sale in California

Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
NSF Approved	Yes
SDS Sheet	LED_Lamp

Copyright 2023 Satco Products, Inc.  
All Rights Reserved

For More Information Visit:  
<https://www.satco.com/>

