

Project Name

Location

Prepared By



SATCO S11780

8.5BR30/LED/5CCT/E26/120V/6PK

Notes

[www] 06-17-2023 22:42:05

General

Status	Active
Watts	8.5W
Incandescent Equivalent	65W
Volts	120V
Shape	BR30
Base	Medium
ANSI Base	E26
Finish	White
CCT (Kelvin)	2700K/3000K/3500K/4000K/5000K
Temperature	Warm White to Natural Light
CRI	90
Lumens	700L
Beam Spread	100
Dimmable	Yes-Dimmable
Hours Rated	25000
Lamp Type	Reflector
Technology	LED

Electrical

Operating Frequency	60Hz
CBCP	250
Power Factor	0.7
Operating Temperature	-20C (-4F) to +45C (+113F)

Physical

MOL	5.06
MOD	3.71
Lensed	Lensed Lamp
Lens Finish	Frost
Lens Material	Plastic
Housing Color	White
Weight (lb.)	0.17

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

Compliance

Safety Listing	cULus - Listed
Location Rating	Damp
Energy Star	No
CA T20 / T24 Rationale	T20 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp