

Project Name

Location

Prepared By



SATCO S11790

5A19/LED/5CCT/E26/120V

Notes

[www] 06-17-2023 22:42:05

General

Status	Active
Watts	5W
Incandescent Equivalent	40W
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	White
CCT (Kelvin)	2700K/3000K/3500K/4000K/5000K
Temperature	Warm White to Natural Light
CRI	90
Lumens	450L
Beam Spread	220
Dimmable	Yes-Dimmable
Hours Rated	25000
Lamp Type	Type A
Technology	LED

Electrical

Operating Frequency	60Hz
Power Factor	0.7
Operating Temperature	-20C (-4F) to +40C (+104F)

Physical

MOL	4.57
MOD	2.36
Housing Color	White
Weight (lb.)	0.1

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	5 Year Limited - 10 hr per day

Compliance

Safety Listing	cULus - Listed
Location Rating	Damp
CA T20 / T24 Rationale	T20 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes
SDS Sheet	LED_Lamp