



Project/Job Name: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Fixture Type: \_\_\_\_\_  
 Notes: \_\_\_\_\_

**S11968** - 10 Watt T8 LED; CCT Selectable; G13 base; 50000 Average rated hours; Type A; Ballast Dependent; 25PK

- CCT Selectable
- Rated for Enclosed Fixture



**ELECTRICAL**

Technology:	LED
Watts:	10W
Volts:	120V-277V
Lumens:	1700L/1750L/1800L
CRI:	83
CCT (Kelvins):	3000K/3500K/4000K
Temperature:	Warm White to Neutral White
Beam Spread :	220
Hours Rated:	50000
Dimmable:	Yes-Dimmable
Dimmable Down To %:	100 to 20 percent
Fluorescent Equivalent :	32W
Operating Temperature :	-20C (-4F) to +45C (+113F)
Ballast Bypass/Direct:	Direct
Ballasting Requirements :	Ballast required, check compatibility
Lamp Ballast Type A/B/C :	Type A
Number of LEDs :	184
THD:	<25
Power Factor :	0.9
Light Source:	LED
Warranty:	5 Year Limited - T8 LED Bulbs

**PACKAGING**

Each UPC:	045923119682
Each Quantity:	1
Each Dimensions:	50.00 x 6.50 x 6.70
Case UPC:	10045923119689
Case Quantity:	25
Case Dimensions:	50.00 x 6.50 x 6.70

**INFO**

Additional Info:	Sold in packs of 25
------------------	---------------------

**PHYSICAL**

ANSI Base:	G13
Base:	Medium Bi Pin
Shape:	T8
Finish:	White
Lens Finish:	Frost
Lens Material:	Glass
MOD (In.):	1.00
MOL (In.):	48.00
Nominal Length:	48.00
Weight (Lbs.):	0.55
Material:	Plastic
Housing Color:	White

**COMPLIANCE**

Safety Listing:	cULus - Listed
Location Rating:	Damp
Indoor/Outdoor:	Indoor
Energy Star Qualified:	No
DLC Approved:	Yes
DLC Classification:	Standard
DLC ID:	S-NRYM8J
DLC Primary Use:	Replacement Lamps (plug and play) (UL Type A)
UL/ETL File Listing:	CN/US - E335148
Rated For Enclosed Fixture:	Yes
SDS Class:	LED_Lamp
Restrictions:	No Restrictions