

Project Name

Location

Prepared By



SATCO S11976

12T8/LED/48-840/DM/A-B

Notes

[www] 10-25-2021 04:00:40

General

Status	Active
Watts	12W
Volts	120V-277V
Ballast Type	Type A/B
Shape	T8
Base	Medium Bi Pin
ANSI Base	G13
Finish	Frost
CCT (Kelvin)	4000
Temperature	Cool White
CRI	82
Lumens	1800L
Beam Spread	210
Dimmable	Yes-Dimmable
Hours Rated	50000
Lamp Type	Linear
Technology	LED

Electrical

Ballasting Requirements	Ballast required (Type A) or Ballast Bypass (Type B)
Operating Frequency	50/60 Hz
Power Factor	0.9
THD	20%
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical

MOL	48.00
MOD	1.00
Lens Finish	Frost
Housing Color	White
Weight (lb.)	0.49

Additional Information

Warranty	5 Year Limited - T8 LED Bulbs
----------	-------------------------------

Compliance

Safety Listing	cULus Listed for Type A; cULus Classified for Type B
Location Rating	Damp
Energy Star	No
California Status	Lawful for sale in California
RoHS Compliant	Yes
FCC Compliant	Yes
NSF Approved	Yes