

Project Name

Location

Prepared By



## SATCO S12124

4.5W/LED/GY6.35/CL/830/12V/1CD

### Notes

[www] 05-15-2024 04:42:54

### General

|                  |               |
|------------------|---------------|
| Status           | Active        |
| Watts            | 4.5W          |
| HID Equivalent   | 40W           |
| Volts            | 12V           |
| Shape            | T6            |
| Base             | Bi Pin GY6.35 |
| ANSI Base        | GY6.35        |
| Finish           | Clear         |
| CCT (Kelvin)     | 3000K         |
| Temperature      | Soft White    |
| CRI              | 80            |
| Lumens           | 430L          |
| Beam Spread      | 300           |
| Dimmable         | Yes-Dimmable  |
| Hours Rated      | 25000         |
| Product Category | Miniature     |
| Technology       | LED           |

### Electrical

|                       |                            |
|-----------------------|----------------------------|
| Operating Frequency   | 60Hz                       |
| Dimming Type          | Phase cut                  |
| Operating Temperature | -20C (-4F) to +40C (+104F) |

### Physical

|               |       |
|---------------|-------|
| MOL           | 1.85  |
| MOD           | 0.71  |
| Housing Color | White |
| Weight (lb.)  | 0.02  |

### Additional Information

|                            |                                                              |
|----------------------------|--------------------------------------------------------------|
| Additional Info            | Housing Material: Ceramic; Lens Material: Polycarbonate (PC) |
| Installation Notes         | Not for use in vapor tight fixtures.                         |
| Rated For Enclosed Fixture | Yes                                                          |
| Warranty                   | 3 Year Limited - Mini LED Pin Base                           |

### Compliance

|                        |                               |
|------------------------|-------------------------------|
| Safety Listing         | cULus - Listed                |
| Location Rating        | Damp                          |
| CA T20 / T24 Rationale | Exempt - Base Not Regulated   |
| California Status      | Lawful for sale in California |
| Title 20 / 24 Status   | Lawful for sale               |
| RoHS Compliant         | Yes                           |