

Project Name

Location

Prepared By

**SATCO S12137**

5W/LED/DC/CL/850/120V/1CD

Notes

(www) 07-31-2024 01:33:00

General

Status	Active
Watts	5W
Incandescent Equivalent	40W
Volts	120V
Shape	T6
Base	Bayonet Double Contact
ANSI Base	BA15d
Finish	Clear
CCT (Kelvin)	5000K
Temperature	Natural Light
CRI	80+
Lumens	550L
Beam Spread	300
Dimmable	Yes-Dimmable
Hours Rated	25000
Product Category	Miniature
Technology	LED

Electrical

Operating Frequency	60Hz
Dimming Type	Forward Phase or Reverse Phase or Phase Selectable
Operating Temperature	-20C (-4F) to +40C (+104F)

Physical

MOL	2.24
MOD	0.75
Housing Color	White
Weight (lb.)	0.05

Additional Information

Additional Info	Housing Material: Ceramic; Lens Material: Polycarbonate (PC)
Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - Mini LED Pin Base

Compliance

Safety Listing	cETLus - Listed
Location Rating	Damp
CA T20 / T24 Rationale	Exempt - Base Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes