

Project Name

Location

Prepared By



SATCO S12138

4.5W/LED/BA15S/CL/830/12V/1CD

Notes

[www] 07-31-2024 01:33:59

General

Status	Active
Watts	4.5W
Incandescent Equivalent	40W
Volts	12V
Shape	T6
Base	Bayonet Single Contact
ANSI Base	BA15s
Finish	Clear
CCT (Kelvin)	3000K
Temperature	Soft White
CRI	80+
Lumens	430L
Beam Spread	300
Dimmable	Yes-Dimmable
Hours Rated	25000
Product Category	Miniature
Technology	LED

Electrical

Operating Frequency	60Hz
Dimming Note	Check the transformer/driver MFG for dimmer compatibility
Operating Temperature	-20C (-4F) to +40C (+104F)

Physical

MOL	2.09
MOD	0.67
Housing Color	White
Weight (lb.)	0.03

Additional Information

Additional Info	Housing Material: Ceramic; Lens Material: Polycarbonate (PC)
Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - Mini LED Pin Base

Compliance

Safety Listing	cULus - Listed
Location Rating	Damp
CA T20 / T24 Rationale	Exempt - Base Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes