

Project Name

Location

Prepared By



SATCO S12261

3.5R14/LED/950/E17/120V

Notes

(www) 07-31-2024 01:33:00

General

Status	Active
Watts	3.5W
Incandescent Equivalent	40W
Volts	120V
Shape	R14
Base	Intermediate
ANSI Base	E17
Finish	Frost
CCT (Kelvin)	5000K
Temperature	Natural Light
CRI	90
Lumens	300L
Beam Spread	110
Dimmable	Yes-Dimmable
Hours Rated	25000
Technology	LED

Electrical

Operating Frequency	60Hz
CBCP	90
Candlepower	90
Power Factor	0.9
Operating Temperature	-25C (-13F) to +45C (+113F)

Physical

MOL	2.56
MOD	1.78
Lens Finish	Frost
Lens Material	Polycarbonate (PC)
Weight (lb.)	0.06

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	5 Year Limited - 10 hr per day

Compliance

Safety Listing	cULus
Location Rating	Damp
CA T20 / T24 Rationale	T20 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes