

Project Name

Location

Prepared By



**SATCO S12314**

4.5W/LED/G4/CL/830/12V

Notes

[www] 05-15-2024 04:42:54

## General

|                  |              |
|------------------|--------------|
| Status           | Active       |
| Watts            | 4.5W         |
| HID Equivalent   | 35W          |
| Volts            | 12V          |
| Shape            | T6           |
| Base             | Bi Pin G4    |
| ANSI Base        | G4           |
| Finish           | Clear        |
| CCT (Kelvin)     | 3000K        |
| Temperature      | Soft White   |
| CRI              | 80           |
| Lumens           | 430L         |
| Beam Spread      | 300          |
| Dimmable         | Yes-Dimmable |
| Hours Rated      | 25000        |
| Product Category | Tubular      |
| Technology       | LED          |

## Electrical

|                       |                            |
|-----------------------|----------------------------|
| Operating Frequency   | 60Hz                       |
| Dimming Type          | Phase cut                  |
| Operating Temperature | -20C (-4F) to +40C (+104F) |

## Physical

|               |       |
|---------------|-------|
| MOL           | 1.81  |
| MOD           | 0.71  |
| Housing Color | Clear |
| Weight (lb.)  | 0.02  |

## Additional Information

|                            |                                      |
|----------------------------|--------------------------------------|
| Installation Notes         | Not for use in vapor tight fixtures. |
| Rated For Enclosed Fixture | Yes                                  |
| Warranty                   | 3 Year Limited - Mini LED Pin Base   |

## Compliance

|                        |                               |
|------------------------|-------------------------------|
| Safety Listing         | cULus - Listed                |
| Location Rating        | Damp                          |
| CA T20 / T24 Rationale | Exempt - Base Not Regulated   |
| California Status      | Lawful for sale in California |
| Title 20 / 24 Status   | Lawful for sale               |
| RoHS Compliant         | Yes                           |